



# Fit-for-use TL5 lamp

## TL5 Essential HE Super 80

Philips TL5 Essential Super80 is a new fluorescent lamp which provides home users and professional end-users an aesthetic miniaturized lighting solution with high reliability at low price.

### Benefits

- 40% less tube dimension than T8 fluorescent lamps. Reducing luminaire, stock and transportation cost
- Slim 16 mm tube allows more compact and flexible luminaire design
- Max lumen output at 35°C ambient temperature, more suitable to actual lighting situation
- Comfortable working and living ambiances with CRI more than 80
- Provides highly reliable and high quality lighting solution at low cost
- Creates atmospheres from warm white to cool daylight

### Features

- Small diameter of 16mm only
- "Cold Chamber" technology
- Applied with electronic ballast for TL5 only
- Operate at temperature from 5°C to 50°C

### Application


- Suitable for use at locations where need compact, high efficient, energy saving lighting. Including offices, shops, supermarkets, schools, hospitals and industrial lighting.

### Warnings and Safety

- 20,000 hours lifetime (50% survival point, 3 hour cycle) with preheat ballast which is ENEC compliant. Lifetime performance may differ on non-ENEC compliant ballasts.

# TL5 Essential HE Super 80

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 Essential 14W/827 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
TL5 Essential 14W/830 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
TL5 Essential 14W/840 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
TL5 Essential 14W/865 1SL/40	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
TL5 Essential 21W/827 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
TL5 Essential 21W/830 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
TL5 Essential 21W/840 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
TL5 Essential 21W/865 1SL/40	17.0 mm	849.0 mm	856.1 mm	853.7 mm	863.2 mm
TL5 Essential 28W/827 1SL/40	17.0 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
TL5 Essential 28W/830 1SL/40	17.0 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
TL5 Essential 28W/840 1SL/40	17.0 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
TL5 Essential 28W/865 1SL/40	17.0 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

General Information	
Cap-Base	G5
Light Technical	
Color rendering index (CRI)	82
Operating and Electrical	
Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg

## General Information

Order Code	Full Product Name	Nominal lifetime
927925982758	TL5 Essential 14W/827 1SL/40	-
927925983058	TL5 Essential 14W/830 1SL/40	15,000 hour(s)
927925984058	TL5 Essential 14W/840 1SL/40	15,000 hour(s)
927925986558	TL5 Essential 14W/865 1SL/40	15,000 hour(s)
927926482758	TL5 Essential 21W/827 1SL/40	-
927926483058	TL5 Essential 21W/830 1SL/40	-

Order Code	Full Product Name	Nominal lifetime
927926484058	TL5 Essential 21W/840 1SL/40	-
927926486558	TL5 Essential 21W/865 1SL/40	-
927926782758	TL5 Essential 28W/827 1SL/40	-
927926783058	TL5 Essential 28W/830 1SL/40	15,000 hour(s)
927926784058	TL5 Essential 28W/840 1SL/40	15,000 hour(s)
927926786558	TL5 Essential 28W/865 1SL/40	15,000 hour(s)

## Light Technical

TL5 Essential HE Super 80

Order Code	Full Product Name	Color Designation	Correlated Color Temperature	Luminous Efficacy (rated)	Luminous Flux
			(Nom)	(Nom)	
927925982758	TL5 Essential 14W/827 1SL/40	Incandescent White	2700 K	88 lm/W	1,350 lm
927925983058	TL5 Essential 14W/830 1SL/40	Warm White (WW)	3000 K	88 lm/W	1,350 lm
927925984058	TL5 Essential 14W/840 1SL/40	Cool White (CW)	4000 K	88 lm/W	1,350 lm
927925986558	TL5 Essential 14W/865 1SL/40	Cool Daylight	6500 K	84 lm/W	1,260 lm
927926482758	TL5 Essential 21W/827 1SL/40	Incandescent White	2700 K	94 lm/W	2,100 lm
927926483058	TL5 Essential 21W/830 1SL/40	Warm White (WW)	3000 K	94 lm/W	2,100 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
927925982758	TL5 Essential 14W/827 1SL/40	14.3 W
927925983058	TL5 Essential 14W/830 1SL/40	14.3 W
927925984058	TL5 Essential 14W/840 1SL/40	14.3 W
927925986558	TL5 Essential 14W/865 1SL/40	14 W
927926482758	TL5 Essential 21W/827 1SL/40	20.8 W
927926483058	TL5 Essential 21W/830 1SL/40	20.8 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927925982758	TL5 Essential 14W/827 1SL/40	-
927925983058	TL5 Essential 14W/830 1SL/40	-
927925984058	TL5 Essential 14W/840 1SL/40	15 kWh
927925986558	TL5 Essential 14W/865 1SL/40	15 kWh
927926482758	TL5 Essential 21W/827 1SL/40	-
927926483058	TL5 Essential 21W/830 1SL/40	23 kWh

Order Code	Full Product Name	Color Designation	Correlated Color Temperature	Luminous Efficacy (rated)	Luminous Flux
			(Nom)	(Nom)	
927926484058	TL5 Essential 21W/840 1SL/40	Cool White (CW)	4000 K	94 lm/W	2,100 lm
927926486558	TL5 Essential 21W/865 1SL/40	Cool Daylight	6500 K	84 lm/W	1,900 lm
927926782758	TL5 Essential 28W/827 1SL/40	Incandescent White	2700 K	94 lm/W	2,900 lm
927926783058	TL5 Essential 28W/830 1SL/40	Warm White (WW)	3000 K	94 lm/W	2,900 lm
927926784058	TL5 Essential 28W/840 1SL/40	Cool White (CW)	4000 K	94 lm/W	2,900 lm
927926786558	TL5 Essential 28W/865 1SL/40	Cool Daylight	6500 K	94 lm/W	2,700 lm

Order Code	Full Product Name	Power Consumption
927926484058	TL5 Essential 21W/840 1SL/40	20.8 W
927926486558	TL5 Essential 21W/865 1SL/40	20.8 W
927926782758	TL5 Essential 28W/827 1SL/40	27.8 W
927926783058	TL5 Essential 28W/830 1SL/40	27.8 W
927926784058	TL5 Essential 28W/840 1SL/40	27.8 W
927926786558	TL5 Essential 28W/865 1SL/40	27.8 W

Order Code	Full Product Name	Energy Consumption kWh/1000 h
927926484058	TL5 Essential 21W/840 1SL/40	-
927926486558	TL5 Essential 21W/865 1SL/40	-
927926782758	TL5 Essential 28W/827 1SL/40	-
927926783058	TL5 Essential 28W/830 1SL/40	31 kWh
927926784058	TL5 Essential 28W/840 1SL/40	31 kWh
927926786558	TL5 Essential 28W/865 1SL/40	31 kWh

## TL5 Essential HE Super 80

