

Efficient fluorescent lighting with improved color rendering

TL-D LIFEMAX Super 80

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

优点

- Good color rendering
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Create atmospheres from warm white to cool daylight

特点


- Highly efficient 3-band fluorescent coating
- High initial light output compared with standard colors
- Low mercury dose
- Can be used with conventional or electronic gear
- Higher efficacy is achieved with electronic gear

应用

- Suitable for use in a wide range of luminaires for TL-D fluorescent lamps for 'human' applications such as schools, offices, shops, factory halls etc.

TL-D LIFEMAX Super 80

二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/830 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 18W/840 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 18W/865 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm
TL-D 30W/840 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
TL-D 30W/865 1SL/25	28 mm	894.6 mm	901.7 mm	899.3 mm	908.8 mm
TL-D 36W/840 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D 36W/865 1SL/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm
TL-D 58W/840 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm
TL-D 58W/865 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

一般信息	
底盖	G13
控制和调光	
可调光	是
机械和外壳	
灯泡外形	T8
审批和申请	
汞 (Hg) 含量 (标称)	2.0 mg

一般信息

Order Code	Full Product Name	标称使用寿命
927980283053	TL-D 18W/830 1SL/25	-
927980284053	TL-D 18W/840 1SL/25	-
927980286553	TL-D 18W/865 1SL/25	-
927981284036	TL-D 30W/840 1SL/25	15,000 小时
927981286536	TL-D 30W/865 1SL/25	15,000 小时

Order Code	Full Product Name	标称使用寿命
927982284053	TL-D 36W/840 1SL/25	-
927982286553	TL-D 36W/865 1SL/25	-
927983284036	TL-D 58W/840 1SL/25	15,000 小时
927983286536	TL-D 58W/865 1SL/25	15,000 小时

灯技术

Order Code	Full Product Name	颜色名称	相关色温 (标称)	显色指数 (CRI)	光效 (额定) (标称)
927980283053	TL-D 18W/830 1SL/25	暖白色 (WW)	3000 K	83	75 lm/W
927980284053	TL-D 18W/840 1SL/25	冷白色 (CW)	4000 K	82	75 lm/W
927980286553	TL-D 18W/865 1SL/25	冷日光	6500 K	80	71 lm/W
927981284036	TL-D 30W/840 1SL/25	冷白色 (CW)	4000 K	82	80 lm/W
927981286536	TL-D 30W/865 1SL/25	冷日光	6500 K	80	77 lm/W
927982284053	TL-D 36W/840 1SL/25	冷白色 (CW)	4000 K	82	90 lm/W

Order Code	Full Product Name	颜色名称	相关色温 (标称)	显色指数 (CRI)	光效 (额定) (标称)
927982286553	TL-D 36W/865 1SL/25	冷日光	6500 K	80	85 lm/W
927983284036	TL-D 58W/840 1SL/25	冷白色 (CW)	4000 K	82	88 lm/W
927983286536	TL-D 58W/865 1SL/25	冷日光	6500 K	80	82 lm/W

操作和电气

TL-D LIFEMAX Super 80

Order Code	Full Product Name	灯具电流 (标称)	电压 (标称)	功耗
927980283053	TL-D 18W/830 1SL/25	0.360 A	59 V	18 W
927980284053	TL-D 18W/840 1SL/25	0.360 A	59 V	18 W
927980286553	TL-D 18W/865 1SL/25	0.360 A	59 V	18 W
927981284036	TL-D 30W/840 1SL/25	0.360 A	98 V	30 W
927981286536	TL-D 30W/865 1SL/25	0.360 A	98 V	30 W

Order Code	Full Product Name	灯具电流 (标称)	电压 (标称)	功耗
927982284053	TL-D 36W/840 1SL/25	0.440 A	103 V	36 W
927982286553	TL-D 36W/865 1SL/25	0.440 A	103 V	36 W
927983284036	TL-D 58W/840 1SL/25	0.670 A	111 V	58.5 W
927983286536	TL-D 58W/865 1SL/25	0.670 A	111 V	58.5 W

