



Product Description

TL-E LIFEMAX Super 80 JIS

Low-pressure mercury discharge lamps with a circular 29 mm tube, complied with Japanese Industrial Standard

Benefits

- /80 colours have good colour rendering ($R_a > 80$) and high efficacy compared with standard colours (R_a 50-70)
- Create atmospheres from warm white to cool daylight

Features

- Available in varying colour designations
- Symmetrical, omnidirectional light Distribution

Application

- Suitable for use in a wide range of luminaires for various purposes, including many decorative luminaires
- Ideal for 'human' applications such as schools, offices, shops, theatres etc.


TL-E LIFEMAX Super 80 JIS

Versions



G10q, C-T9

Dimensional drawing



Product	D (max)	D (min)	E (max)	I (min)	I (max)
TL-E 40W/865 JIS 1CT/12	30.8 mm	27.1 mm	381 mm	309.0 mm	321.0 mm

