



Circular shaped, basic fluorescent lighting

TL-E LIFEMAX Standard Colours

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.

Benefits

- Standard colours with moderate colour rendering (R a 50 - 70)
- Create atmospheres from warm white to cool daylight

Features

- Available in varying colour designations
- Symmetrical, omni-directional light distribution

Application

- Suitable for use in a wide range of luminaires for various purposes, including many decorative luminaires
- Ideal for 'human' applications such as schools, offices, shops, theatres etc. where colour rendering is not an important factor


TL-E LIFEMAX Standard Colours

Versions



LPPR TL-ESTD G10q

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
TL-E 22W/54-765 1CT/20	30.9 mm	26.2 mm	205.0 mm	213.5 mm	149.1 mm	155.6 mm
TL-E 32W/54-765 1CT/20	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

General Information	
Cap-Base	G10q
Nominal lifetime	8,000 hour(s)
Light Technical	
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	72
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T29
Approval and Application	
Mercury (Hg) Content (Nom)	9 mg

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
928026205436	TL-E 22W/54-765 1CT/20	48 lm/W	1,050 lm
928026305436	TL-E 32W/54-765 1CT/20	57 lm/W	1,750 lm

Operating and Electrical

Order Code	Full Product Name	Lamp		
		Current (Nom)	Voltage (Nom)	Power Consumption
928026205436	TL-E 22W/54-765 1CT/20	0.400 A	62 V	22.0 W

TL-E LIFEMAX Standard Colours

Order Code	Full Product Name	Lamp	Voltage (Nom)	Power Consumption
		Current (Nom)		
928026305436	TL-E 32W/54-765	0.450 A	81 V	32.0 W
	1CT/20			

