



# ColorReach Compact Powercore RGBW/RGBA – Premium long-throw exterior LED floodlight with intelligent colour light

## ColorReach Compact Powercore RGBW/RGBA

ColorReach Compact Powercore RGBA/RGBW combines all the benefits of LED-based lighting and control in a premium exterior long-throw dynamic colour-changing luminaire for lighting tall buildings, bridges and iconic structures. This compact luminaire delivers intense, energy-efficient output at a reasonable price, opening up new possibilities for exterior illumination. ColorReach Compact Powercore offers a range of accessories that allow for customisable beam angles for floodlighting, spotlighting, wall washing and grazing, along with the efficiency and cost-effectiveness of Powercore technology in a rugged die-cast aluminium housing. Custom configurations with custom channels of white or colour LED sources are also available to support special applications.

### Benefits

- 4-channel
- Colour consistency and beam uniformity
- Suitable for long-throw, high-punch applications
- Complete set of accessories

# ColorReach Compact Powercore RGBW/RGBA

## Features

- Powercore® technology to directly accept line voltage
- Estimated output of over 5,500 lumens when full-on
- Custom-designed 5° collimator optic
- Optional spread lenses of 8°, 13°, 23°, 43°, 63°, and 5° x 17°
- Rugged mounting bracket allows simple positioning and fixture rotation
- Complete set of accessories including glare shields and glare mask (cut-off 45°) attach directly to secondary diffuser trim bezels

## Application

- Illumination of large architectural façades
- Designed for large-scale installation, e.g. commercial skyscrapers, casinos, large retail exteriors, bridges, piers, public monuments and themed attractions

## Versions



## Product details

ColorReach Compact Powercore  
four channel floodlight LED fixture  
back view



ColorReach Compact Powercore  
four channel floodlight LED fixture  
front view



ColorReach Compact Powercore  
four channel floodlight LED fixture  
side view



## ColorReach Compact Powercore RGBW/RGBA

