



# Dynamic RGB wall washer LED linear luminaire

## UNIstrip G2 RGB

UNIstrip G2 is a LED lighting fixture designed for wide range architecture wall washer lighting applications. UNIstrip G2 offers reliable quality and outstanding performance

### Benefits

- Outstanding performance with color uniformity
- Reliable quality for long term outdoor applications
- Low investment cost

### Features

- Dynamic RGB effect with short color mixing distance
- Reliable waterproof with protective vent, IP66
- Two typical beam angle options for wall washer application
- Ensure the consistency of mass production with color calibration

### Application

- Building Facade/Bridge

# UNIstrip G2 RGB

## Versions



BCP280 G2

### Application Conditions

Maximum dim level	0% (digital)
-------------------	--------------

### Approval and Application

Mech. impact protection code	IK06
------------------------------	------

### Controls and Dimming

Dimmable	Yes
----------	-----

### General Information

CE mark	CE mark
Light source color	Red, green and blue
Optical cover/lens type	Polycarbonate small
Driver included	No
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit

### Initial Performance (IEC Compliant)

Init. Corr. Color Temperature	- K
Init. Color Rendering Index	-

### Light Technical

Standard tilt angle side entry	-
Standard tilt angle posttop	-

### Mechanical and Housing

Color	Aluminum and black
-------	--------------------

### General Information

Order Code	Full Product Name	Optic type
911401621003	BCP280 G2 9xLED-HP/RGB 24V L313 NB	-
911401621103	BCP280 G2 9xLED-HP/RGB 24V L313 WB	Wide beam angle 50°
911401621203	BCP280 G2 36xLED-HP/RGB 24V L1190 NB	-
911401621403	BCP280 G2 36xLED-HP/RGB 24V L1190 WB	Wide beam angle 50°

## Initial Performance (IEC Compliant)

## UNlstrip G2 RGB

Order Code	Full Product Name	Initial luminous flux
911401621003	BCP280 G2 9xLED-HP/RGB 24V L313 NB	570 lm
911401621103	BCP280 G2 9xLED-HP/RGB 24V L313 WB	570 lm

Order Code	Full Product Name	Initial luminous flux
911401621203	BCP280 G2 36xLED-HP/RGB 24V L1190 NB	2280 lm
911401621403	BCP280 G2 36xLED-HP/RGB 24V L1190 WB	2280 lm

