



Ledinaire FloodlightSimply great LED

Ledinaire floodlight maxi

The Ledinaire range contains a selection of popular off-the-shelf LED luminaires that come with the Philips high-quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

Benefits

- Philips quality and reliability
- Energy saving: 1:1 retrofit up to HPI-TP 400 W
- Quick installation without opening the floodlight
- Philips high-quality finish, robust and fully reliable

Features

- Highly efficient: 100 lm/W Two system flux models: 10 klm/100 W and 20 klm/200 W
- Long lifetime of 50,000 hours (Ta 25 °C)
- Robust (IK08) and waterproof (IP65)
- floodlights0.5 m prewired cable (class1)
- Standing-up or hanging-down mounting
- Compliant with CE, CB, ROHS
- Salt spray 500 hours
- Clear tempered glassLOR >86

Application

- Car parks
- Industrial areas
- Dock yards
- Security/amenity lighting

Specifications

Aiming Horizontal	to °	Aiming Vertical	to °
-------------------	------	-----------------	------

Ledinaire floodlight maxi

AverageAmbientTempe	-25 to +40 °C
rature	
Beam angle	100° x 100°
Color	Grey and Grey
	Grey painting RAL 7043
	Flying leads/wires (Flying leads/wires)
	no
	Power supply unit (PSU)
	4000 K
	4,000 K
	100 lm/W
	100 lm/W
	20000 lm
	50 to 60 Hz
	220 to 240 V

	43 A
Light Source	SMD LED
	No
Maintenance	Maintenance c
Material	Housing: aluminium die-cast
Material of Reflector	Reflector: aluminium
	Beam category A1 (A1)
	Specular aluminium reflector
Remarks	Installation on mast-head frames/walls or on roofs or ceilings/ walls.
	Standing-up or hanging-down mounting.
	U-shaped mounting bracket with a foot-print suitable for 3- point fixation by means of M20 bolts.
	3 years

Versions



LED Module, system flux 20,000
lm - LED - 100° x 100°

Product details



Ledinaire-
BVP106_Led100-1DPP.TIF



Ledinaire-
BVP106_Led100-2DPP.TIF

Ledinaire floodlight maxi

Product details



Ledinaire-
BVP106_Led100-3DPP.TIF



Ledinaire-
BVP106_Led100-4DPP.TIF



Ledinaire-
BVP106_Led100-5DPP.TIF



Ledinaire-
BVP106_Led200-1DPP.TIF



Ledinaire-
BVP106_Led200-2DPP.TIF



Ledinaire-
BVP106_Led200-3DPP.TIF



Ledinaire-
BVP106_Led200-4DPP.TIF



Ledinaire-
BVP106_Led200-5DPP.TIF

Ledinaire floodlight maxi

