



Miniaturized downlight with leading optical performance and great diversity

LuxSpace G4

LuxSpace Gen4 is the a new LED downlight range combining light comfort and leading performance with luxury looking

Benefits

- Visual comfort
- Multiple options for various applications
- Smart lighting

Features

- Miniaturized form factor
- High optical efficiency
- Great product diversity
- Tunable white

Application

- Office
- shopping mall
- hotel
- retail

Specifications

LuxSpace G4

Mounting type	Recessed
Operating Temperature range	-20 to +40 °C
Light Source	LED module
Mains Voltage	220-240V AC / 50-60Hz
Dimming	PSU: non-dimmable PSD: Dimmable via Dali protocol WIA: Wireless control POE: Power over Ethernet
Control system input	DALI / POE /WIA
Material	Housing: die-cast aluminum
Main color of the luminaire	Black & White
Lumen maintenance at median useful life	L70 50.000h
Flicker / Pst / SVM	<4%
Luminous flux	740lm, 1000lm, 1500lm, 2000lm, 2600lm, 3400lm, 4300lm @840
Power consumption	6.6-39.7W

Luminaire efficacy	97-127 lm/W @840
Correlated color temperature - CCT	3000K, 4000K, Tunable White
Color Rendering index - CRI	80, 90
Beam angle	32°-36° 56°-63°
Reflector material	Plastic, Aluminum coated
Optic	AL coating Office compliant UGR<19 (OC)
Mechanical impact protection	IK02, IK03
Ingress protection	IP20 / IP54 (front side)
Light source replaceable	No
Driver replaceable	Yes
Overall diameter	D100,D125,D150,D200
UGR	19
Installation	recessed Fixation by means of spring fasteners



Versions











LuxSpace G4

Luxspace G4


Dimensional drawing



Dimensional drawing



Dimensional drawing



General Information	
CE mark	CE mark
ENEC mark	-
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Initial chromaticity	-

General Information

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Light source replaceable	Number of gear units
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Light source replaceable	Number of gear units
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Light source replaceable	Number of gear units
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit

Order Code	Full Product Name	Driver included	Flammability mark	Glow-wire test	Light source replaceable	Number of gear units
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	Yes	For mounting on normally flammable surfaces	Temperature 650 °C, duration 30 s	No	1 unit
911401567271	DN588B LED6/940 PSD C D100 WH CAU	-	-	-	-	-
911401567471	DN589B LED10/940 PSD C D150 WH CAU	-	-	-	-	-
911401567671	DN590B LED15/940 PSD C D150 WH CAU	-	-	-	-	-

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	-	4000 K	Reflector	>90	112 lm/W	740 lm	Facetted reflector with beam angle 60°
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	-	4000 K	Reflector	>90	112 lm/W	740 lm	Facetted reflector with beam angle 30°
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	-	3000 K	Reflector	>80	103 lm/W	960 lm	Facetted reflector with beam angle 60°
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	-	4000 K	Reflector	>90	108 lm/W	1,000 lm	Facetted reflector with beam angle 60°
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	-	4000 K	Reflector	>90	92 lm/W	860 lm	Facetted reflector with beam angle 60°
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	-	4000 K	Reflector	>90	108 lm/W	1,000 lm	Facetted reflector with beam angle 60°
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	-	3000 K	Reflector	>80	104 lm/W	1,410 lm	Facetted reflector with beam angle 60°
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	-	4000 K	Reflector	>90	111 lm/W	1,500 lm	Facetted reflector with beam angle 60°

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	-	4000 K	Reflector	>90	94 lm/W	1,270 lm	Facetted reflector with beam angle 60°
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	-	4000 K	Reflector	>90	111 lm/W	1,500 lm	Facetted reflector with beam angle 30°
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	-	4000 K	Reflector	>90	111 lm/W	1,500 lm	Facetted reflector with beam angle 60°
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	-	4000 K	Reflector	>90	94 lm/W	1,270 lm	Facetted reflector with beam angle 60°
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	-	4000 K	Reflector	>90	93 lm/W	1,800 lm	Facetted reflector with beam angle 60°
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	-	4000 K	Reflector	>90	109 lm/W	2,100 lm	Facetted reflector with beam angle 30°
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	-	4000 K	Reflector	>90	109 lm/W	2,100 lm	Facetted reflector with beam angle 60°
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	-	3000 K	Reflector	>80	103 lm/W	680 lm	Facetted reflector with beam angle 60°
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	-	4000 K	Reflector	>80	108 lm/W	710 lm	Facetted reflector with beam angle 60°
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	-	4000 K	Reflector	>90	111 lm/W	2,150 lm	Facetted reflector with beam angle 60°
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	-	3000 K	Reflector	>80	109 lm/W	2,100 lm	Facetted reflector with beam angle 30°
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	-	3000 K	Reflector	>80	109 lm/W	2,100 lm	Facetted reflector with beam angle 60°
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	-	4000 K	Reflector	>90	113 lm/W	2,600 lm	Facetted reflector with beam angle 60°
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	-	3000 K	Reflector	>80	109 lm/W	2,510 lm	Facetted reflector with beam angle 30°
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	-	4000 K	Reflector	>90	113 lm/W	2,600 lm	Facetted reflector with beam angle 30°
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	-	4000 K	Reflector	>90	113 lm/W	2,600 lm	Facetted reflector with beam angle 60°
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	-	4000 K	Reflector	>90	113 lm/W	2,600 lm	Facetted reflector with beam angle 30°
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	-	3000 K	Reflector	>80	102 lm/W	3,300 lm	Facetted reflector with beam angle 60°
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	-	4000 K	Reflector	>80	105 lm/W	3,400 lm	Facetted reflector with beam angle 60°
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	-	4000 K	Reflector	>90	91 lm/W	2,970 lm	Facetted reflector with beam angle 60°
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	-	4000 K	Reflector	>90	91 lm/W	2,970 lm	Facetted reflector with beam angle 30°
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	-	3000 K	Reflector	>80	103 lm/W	4,100 lm	Facetted reflector with beam angle 60°
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	-	4000 K	Reflector	>80	108 lm/W	4,300 lm	Facetted reflector with beam angle 60°
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	-	4000 K	Reflector	>90	93 lm/W	3,700 lm	Facetted reflector with beam angle 60°

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	-	3000 K	Reflector	>80	103 lm/W	4,100 lm	Facetted reflector with beam angle 30°
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	-	4000 K	Reflector	>80	108 lm/W	4,300 lm	Facetted reflector with beam angle 30°
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	-	4000 K	Reflector	>80	125 lm/W	1,050 lm	Facetted reflector with beam angle 60°
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	-	3000 K	Reflector	>80	176 lm/W	1,480 lm	Facetted reflector with beam angle 60°
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	-	4000 K	Reflector	>80	185 lm/W	1,550 lm	Facetted reflector with beam angle 60°
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	-	3000 K	Reflector	>80	113 lm/W	2,030 lm	Facetted reflector with beam angle 60°
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	-	4000 K	Reflector	>80	119 lm/W	2,150 lm	Facetted reflector with beam angle 60°
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	-	3000 K	Reflector	>80	102 lm/W	3,300 lm	Facetted reflector with beam angle 60°
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	-	4000 K	Reflector	>80	105 lm/W	3,400 lm	Facetted reflector with beam angle 60°
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	-	3000 K	Reflector	>80	103 lm/W	4,100 lm	Facetted reflector with beam angle 60°
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	-	4000 K	Reflector	>80	108 lm/W	4,300 lm	Facetted reflector with beam angle 60°
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	-	4000 K	Reflector	>80	125 lm/W	1,050 lm	Facetted reflector with beam angle 60°
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	-	4000 K	Reflector	>80	115 lm/W	1,550 lm	Facetted reflector with beam angle 60°
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	-	3000 K	Reflector	>80	105 lm/W	2,030 lm	Facetted reflector with beam angle 60°
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	-	4000 K	Reflector	>80	111 lm/W	2,150 lm	Facetted reflector with beam angle 60°
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	-	4000 K	Reflector	>80	108 lm/W	4,300 lm	Facetted reflector with beam angle 60°
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	-	3000 K	Reflector	>80	112 lm/W	940 lm	Facetted reflector with beam angle 60°
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	-	4000 K	Reflector	>80	119 lm/W	1,000 lm	Facetted reflector with beam angle 60°
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	-	4000 K	Reflector	>80	109 lm/W	1,470 lm	Facetted reflector with beam angle 60°
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	-	4000 K	Reflector	>80	113 lm/W	2,040 lm	Facetted reflector with beam angle 60°
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	-	4000 K	Reflector	>80	99 lm/W	3,230 lm	Facetted reflector with beam angle 60°
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	-	4000 K	Reflector	>80	103 lm/W	4,090 lm	Facetted reflector with beam angle 60°
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	-	3000 K	Reflector	>80	107 lm/W	1,930 lm	Facetted reflector with beam angle 60°
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	-	4000 K	Reflector	>80	99 lm/W	3,230 lm	Facetted reflector with beam angle 60°

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	-	4000 K	Reflector	>80	103 lm/W	4,090 lm	Facetted reflector with beam angle 60°
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	-	3000 K	Reflector	>80	25 lm/W	990 lm	Facetted reflector with beam angle 60°
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	-	4000 K	Reflector	>80	125 lm/W	1,050 lm	Facetted reflector with beam angle 60°
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	-	4000 K	Reflector	>80	115 lm/W	1,550 lm	Facetted reflector with beam angle 60°
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	-	4000 K	Reflector	>80	108 lm/W	4,300 lm	Facetted reflector with beam angle 60°
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	-	4000 K	Reflector	>80	109 lm/W	1,470 lm	Facetted reflector with beam angle 60°
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	-	3000 K	Reflector	>80	107 lm/W	1,930 lm	Facetted reflector with beam angle 60°
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	32 degree(s)	6500 K	Reflector	>80	88 lm/W	2,200 lm	Facetted reflector with beam angle 36°
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	62 degree(s)	2700 K	Reflector	>80	88 lm/W	2,200 lm	Facetted reflector with beam angle 60°
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	62 degree(s)	2700 K	Reflector	>80	88 lm/W	2,200 lm	Facetted reflector with beam angle 60°
911401567271	DN588B LED6/940 PSD C D100 WH CAU	-	4000 K	-	>90	84.11423376623377 lm/W	647.6796 lm	-
911401567471	DN589B LED10/940 PSD C D150 WH CAU	-	4000 K	-	>90	98.33192307692309 lm/W	1,150.4835 lm	-
911401567671	DN590B LED15/940 PSD C D150 WH CAU	-	4000 K	-	>90	101.94157594936709 lm/W	1,610.6769000000002 lm	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	6.6 W	911401543341	DN591B LED20/830 PSD C D150 WH WB GC	19.3 W
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	6.6 W	911401544241	DN592B LED25/840 PSU C D150 WH WB GC	23 W
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	9.3 W	911401544541	DN592B LED25/830 PSU C D150 WH MB GC	23 W
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	9.3 W	911401544641	DN592B LED25/840 PSU C D150 WH MB GC	23 W
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	9.3 W	911401545041	DN592B LED25/840 PSD C D150 WH WB GC	23 W
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	9.3 W	911401545441	DN592B LED25/840 PSD C D150 WH MB GC	23 W
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	13.5 W	911401545941	DN593B LED30/830 PSU C D200 WH WB GC	32.5 W
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	13.5 W	911401546041	DN593B LED30/840 PSU C D200 WH WB GC	32.5 W
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	13.5 W	911401546241	DN593B LED30/940 PSU C D200 WH WB GC	32.5 W
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	13.5 W	911401546641	DN593B LED30/940 PSU C D200 WH MB GC	32.5 W
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	13.5 W	911401546741	DN594B LED40/830 PSU C D200 WH WB GC	39.7 W
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	13.5 W	911401546841	DN594B LED40/840 PSU C D200 WH WB GC	39.7 W
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	19.3 W	911401547041	DN594B LED40/940 PSU C D200 WH WB GC	39.7 W
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	19.3 W	911401547141	DN594B LED40/830 PSU C D200 WH MB GC	39.7 W
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	19.3 W	911401547241	DN594B LED40/840 PSU C D200 WH MB GC	39.7 W
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	6.6 W	911401547841	DN589B LED10/840 PSU C D150 WH WB GM	8.4 W
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	6.6 W	911401547941	DN590B LED15/830 PSU C D150 WH WB GM	8.4 W
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	19.3 W	911401548041	DN590B LED15/840 PSU C D150 WH WB GM	8.4 W
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	19.3 W	911401548141	DN591B LED20/830 PSU C D200 WH WB GM	18 W

Order Code	Full Product Name	Power Consumption
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	18 W
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	32.5 W
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	32.5 W
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	39.7 W
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	39.7 W
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	8.4 W
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	13.5 W
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	19.3 W
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	19.3 W
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	39.7 W
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	8.4 W
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	8.4 W
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	13.5 W
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	18 W
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	32.5 W
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	39.7 W

Order Code	Full Product Name	Power Consumption
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	18 W
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	32.5 W
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	39 W
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	10.5 W
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	10.5 W
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	13.8 W
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	39 W
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	13.8 W
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	17.5 W
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	25 W
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	25 W
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	25 W
911401567271	DN588B LED6/940 PSD C D100 WH CAU	7.7 W
911401567471	DN589B LED10/940 PSD C D150 WH CAU	11.7 W
911401567671	DN590B LED15/940 PSD C D150 WH CAU	15.8 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	No
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	No
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	No
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	No
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	No
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	Yes
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	No
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	No
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	No
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	No
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	Yes
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	Yes
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	No
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	No
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	Yes
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	No
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	No
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	No
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	No
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	Yes
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	No
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	No
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	No
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	Yes
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	Yes
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	No
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	No
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	No
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	No
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	No
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	No
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	No

Order Code	Full Product Name	Dimmable
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	No
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	No
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	No
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	No
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	No
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	No
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	No
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	No
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	No
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	No
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	No
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	Yes
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	Yes
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	Yes
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	Yes
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	Yes
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	No
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	No
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	No
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	No
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	No
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	No
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	Yes
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	Yes
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	Yes
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	Yes
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	Yes
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	Yes
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	Yes
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	Yes
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	Yes
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	Yes

Order Code	Full Product Name	Dimmable
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	Yes
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	Yes
911401567271	DN588B LED6/940 PSD C D100 WH CAU	Yes

Order Code	Full Product Name	Dimmable
911401567471	DN589B LED10/940 PSD C D150 WH CAU	Yes
911401567671	DN590B LED15/940 PSD C D150 WH CAU	Yes

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	White and black
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	White and black
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	White and black
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	White and black
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	White and black
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	White and black
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	White and black
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	White and black
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	White and black
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	White and black
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	White and black
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	White and black
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	White and black
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	White and black
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	White and black
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	White and black
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	White and black
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	White and black
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	White and black
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	White and black
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	White and black
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	White and black
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	White and black
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	White and black
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	White and black
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	White and black
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	White and black
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	White and black
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	White and black
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	White and black
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	White and black
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	White and black
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	White and black
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	White and black
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	White and black

Order Code	Full Product Name	Housing Color
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	White and black
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	White and black
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	White and black
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	White and black
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	White and black
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	White and black
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	White and black
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	White and black
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	White and black
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	White and black
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	White and black
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	White and black
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	White and black
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	White and black
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	White and black
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	White and black
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	White and black
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	White and black
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	White and black
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	White and black
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	White and black
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	White and black
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	White and black
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	White and black
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	White and black
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	White and black
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	White and black
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	White and black
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	White and black
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	White and black
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	White and black
911401567271	DN588B LED6/940 PSD C D100 WH CAU	-
911401567471	DN589B LED10/940 PSD C D150 WH CAU	-
911401567671	DN590B LED15/940 PSD C D150 WH CAU	-

Approval and Application

Order Code	Full Product Name	Protection class	Mech. impact protection	Ingress protection
		IEC	code	code
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	Safety class II	IK03	IP20

Order Code	Full Product Name	Protection class	Mech. impact protection	Ingress protection
		IEC	code	code
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	Safety class II	IK03	IP20

Order Code	Full Product Name	Protection class IEC	Mech. impact protection code	Ingress protection code
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	Safety class II	IK03	IP20
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	Safety class II	IK03	IP20
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	Safety class II	IK03	IP20
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	Safety class II	IK03	IP20
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	Safety class II	IK03	IP20
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	Safety class II	IK03	IP20
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	Safety class II	IK03	IP20
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	Safety class II	IK03	IP20
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	Safety class I	IK03	IP20
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	Safety class I	IK03	IP20
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	Safety class II	IK03	IP20
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	Safety class II	IK03	IP20
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	Safety class I	IK03	IP20
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	Safety class II	IK03	IP20/54
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	Safety class II	IK03	IP20/54
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	Safety class II	IK03	IP20
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	Safety class II	IK03	IP20
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	Safety class I	IK03	IP20
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	Safety class II	IK03	IP20
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	Safety class II	IK03	IP20
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	Safety class II	IK03	IP20
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	Safety class I	IK03	IP20
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	Safety class I	IK03	IP20
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	Safety class II	IK03	IP20

Order Code	Full Product Name	Protection class IEC	Mech. impact protection code	Ingress protection code
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	Safety class II	IK03	IP20
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	Safety class II	IK03	IP20
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	Safety class II	IK03	IP20
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	Safety class II	IK03	IP20
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	Safety class II	IK03	IP20
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	Safety class II	IK03	IP20
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	Safety class II	IK03	IP20
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	Safety class II	IK03	IP20
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	Safety class II	IK03	IP20
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	Safety class II	IK03	IP20
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	Safety class II	IK03	IP20
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	Safety class II	IK03	IP20
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	Safety class II	IK03	IP20
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	Safety class II	IK03	IP20
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	Safety class II	IK03	IP20
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	Safety class II	IK03	IP20
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	Safety class II	IK03	IP20
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	Safety class II	IK03	IP20
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	Safety class I	IK03	IP20
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	Safety class I	IK03	IP20
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	Safety class I	IK03	IP20
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	Safety class I	IK03	IP20
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	Safety class II	IK03	IP20/54
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	Safety class II	IK03	IP20/54

Order Code	Full Product Name	Mech.		
		Protection class	impact protection	Ingress protection
Order Code	Full Product Name	IEC	code	code
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	Safety class II	IK03	IP20/54
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	Safety class II	IK03	IP20/54
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	Safety class II	IK03	IP20/54
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	Safety class II	IK03	IP20/54
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	Safety class I	IK03	IP20/54
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	Safety class I	IK03	IP20/54
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	Safety class I	IK03	IP20/54
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	Safety class II	IK03	IP20
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	Safety class II	IK03	IP20
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	Safety class I	IK03	IP20

Order Code	Full Product Name	Mech.		
		Protection class	impact protection	Ingress protection
Order Code	Full Product Name	IEC	code	code
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	Safety class I	IK03	IP20
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	Safety class I	IK03	IP20/54
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	Safety class I	IK03	IP20/54
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	Safety class II	IK03	IP20
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	Safety class II	IK03	IP20
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	Safety class II	IK03	IP20
911401567271	DN588B LED6/940 PSD C D100 WH CAU	Safety class II	IK02	IP20
911401567471	DN589B LED10/940 PSD C D150 WH CAU	Safety class II	IK02	IP20
911401567671	DN590B LED15/940 PSD C D150 WH CAU	Safety class II	IK02	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Luminous flux tolerance
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	+/-10%
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	+/-10%
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	+/-10%
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	+/-10%
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	+/-10%
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	+/-10%
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	+/-10%
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	+/-10%
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	+/-10%
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	+/-10%
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	+/-10%
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	+/-10%
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	+/-10%
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	+/-10%
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	+/-10%
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	+/-10%
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	+/-10%
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	+/-10%
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	+/-10%
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	+/-10%
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	+/-10%
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	+/-10%
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	+/-10%
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	+/-10%
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	+/-10%
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	+/-10%
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	+/-10%
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	+/-10%
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	+/-10%
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	+/-10%
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	+/-10%
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	+/-10%
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	+/-10%
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	+/-10%
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	+/-10%
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	+/-10%
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	+/-10%
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	+/-10%
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	+/-10%
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	+/-10%
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	+/-10%
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	+/-10%
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	+/-10%
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	+/-10%
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	+/-10%
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	+/-10%
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	+/-10%
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	+/-10%
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	+/-10%
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	+/-10%
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	+/-10%
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	+/-10%
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	+/-10%
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	+/-10%
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	+/-10%
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	+/-10%
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	+/-10%

Order Code	Full Product Name	Luminous flux tolerance
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	+/-10%
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	+/-10%
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	+/-10%
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	+/-10%
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	+/-15%
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	+/-15%
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	+/-15%
911401567271	DN588B LED6/940 PSD C D100 WH CAU	+/-10%
911401567471	DN589B LED10/940 PSD C D150 WH CAU	+/-10%
911401567671	DN590B LED15/940 PSD C D150 WH CAU	+/-10%

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	1 %	50,000 hour(s)	21,000 hour(s)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	1 %	50,000 hour(s)	21,000 hour(s)
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	1 %	50,000 hour(s)	21,000 hour(s)
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	1 %	50,000 hour(s)	21,000 hour(s)
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	1 %	50,000 hour(s)	21,000 hour(s)
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	1 %	50,000 hour(s)	21,000 hour(s)
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	1 %	50,000 hour(s)	21,000 hour(s)
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	1 %	50,000 hour(s)	21,000 hour(s)
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	1 %	50,000 hour(s)	21,000 hour(s)
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	1 %	50,000 hour(s)	21,000 hour(s)
911401567271	DN588B LED6/940 PSD C D100 WH CAU	-	-	-
911401567471	DN589B LED10/940 PSD C D150 WH CAU	-	-	-
911401567671	DN590B LED15/940 PSD C D150 WH CAU	-	-	-

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401536741	DN588B LED6/840 PSU C D100 WH WB GC	Not applicable
911401537141	DN588B LED6/840 PSU C D100 WH MB GC	Not applicable
911401537441	DN589B LED10/830 PSU C D125 WH WB GC	Not applicable
911401537541	DN589B LED10/840 PSU C D125 WH WB GC	Not applicable
911401537741	DN589B LED10/940 PSU C D125 WH WB GC	Not applicable
911401538341	DN589B LED10/840 PSD C D125 WH WB GC	1%
911401539041	DN590B LED15/830 PSU C D125 WH WB GC	Not applicable
911401539141	DN590B LED15/840 PSU C D125 WH WB GC	Not applicable
911401539341	DN590B LED15/940 PSU C D125 WH WB GC	Not applicable
911401539541	DN590B LED15/840 PSU C D125 WH MB GC	Not applicable

Order Code	Full Product Name	Maximum dim level
911401539941	DN590B LED15/840 PSD C D125 WH WB GC	1%
911401540141	DN590B LED15/940 PSD C D125 WH WB GC	1%
911401541241	DN591B LED20/940 PSU C D125 WH WB GC	Not applicable
911401541441	DN591B LED20/840 PSU C D125 WH MB GC	Not applicable
911401541841	DN591B LED20/840 PSD C D125 WH WB GC	1%
911401549541	DN588B LED6/830 PSU C D125 WH WB WP GM	Not applicable
911401549641	DN588B LED6/840 PSU C D125 WH WB WP GM	Not applicable
911401542641	DN591B LED20/840 PSU C D150 WH WB GC	Not applicable
911401542941	DN591B LED20/830 PSU C D150 WH MB GC	Not applicable
911401543341	DN591B LED20/830 PSD C D150 WH WB GC	1%

Order Code	Full Product Name	Maximum dim level
911401544241	DN592B LED25/840 PSU C D150 WH WB GC	Not applicable
911401544541	DN592B LED25/830 PSU C D150 WH MB GC	Not applicable
911401544641	DN592B LED25/840 PSU C D150 WH MB GC	Not applicable
911401545041	DN592B LED25/840 PSD C D150 WH WB GC	1%
911401545441	DN592B LED25/840 PSD C D150 WH MB GC	1%
911401545941	DN593B LED30/830 PSU C D200 WH WB GC	Not applicable
911401546041	DN593B LED30/840 PSU C D200 WH WB GC	Not applicable
911401546241	DN593B LED30/940 PSU C D200 WH WB GC	Not applicable
911401546641	DN593B LED30/940 PSU C D200 WH MB GC	Not applicable
911401546741	DN594B LED40/830 PSU C D200 WH WB GC	Not applicable
911401546841	DN594B LED40/840 PSU C D200 WH WB GC	Not applicable
911401547041	DN594B LED40/940 PSU C D200 WH WB GC	Not applicable
911401547141	DN594B LED40/830 PSU C D200 WH MB GC	Not applicable
911401547241	DN594B LED40/840 PSU C D200 WH MB GC	Not applicable
911401547841	DN589B LED10/840 PSU C D150 WH WB GM	Not applicable
911401547941	DN590B LED15/830 PSU C D150 WH WB GM	Not applicable
911401548041	DN590B LED15/840 PSU C D150 WH WB GM	Not applicable
911401548141	DN591B LED20/830 PSU C D200 WH WB GM	Not applicable
911401548241	DN591B LED20/840 PSU C D200 WH WB GM	Not applicable
911401548341	DN593B LED30/830 PSU C D200 WH WB GM	Not applicable
911401548441	DN593B LED30/840 PSU C D200 WH WB GM	Not applicable
911401548541	DN594B LED40/830 PSU C D200 WH WB GM	Not applicable
911401548641	DN594B LED40/840 PSU C D200 WH WB GM	Not applicable
911401548941	DN589B LED10/840 PSD C D150 WH WB GM	1%
911401549041	DN590B LED15/840 PSD C D150 WH WB GM	1%

Order Code	Full Product Name	Maximum dim level
911401549141	DN591B LED20/830 PSD C D200 WH WB GM	1%
911401549241	DN591B LED20/840 PSD C D200 WH WB GM	1%
911401549441	DN594B LED40/840 PSD C D200 WH WB GM	1%
911401549741	DN589B LED10/830 PSU C D150 WH WB WP GM	Not applicable
911401549841	DN589B LED10/840 PSU C D150 WH WB WP GM	Not applicable
911401550041	DN590B LED15/840 PSU C D150 WH WB WP GM	Not applicable
911401550241	DN591B LED20/840 PSU C D200 WH WB WP GM	Not applicable
911401550341	DN593B LED30/840 PSU C D200 WH WB WP GM	Not applicable
911401550441	DN594B LED40/840 PSU C D200 WH WB WP GM	Not applicable
911401550941	DN591B LED20/830 PSD C D200 WH WB WP GM	1%
911401551141	DN593B LED30/840 PSD C D200 WH WB WP GM	1%
911401551241	DN594B LED40/840 PSD C D200 WH WB WP GM	1%
911401552041	DN589B LED10/830 PSD C D150 WH WB CAU	1%
911401552141	DN589B LED10/840 PSD C D150 WH WB CAU	1%
911401552241	DN590B LED15/840 PSD C D150 WH WB CAU	1%
911401552641	DN594B LED40/840 PSD C D200 WH WB CAU	1%
911401553641	DN590B LED15/840 PSD C D150 WH WB WP CAU	1%
911401553741	DN591B LED20/830 PSD C D200 WH WB WP CAU	1%
911401542251	DN591B LED20/TWH PSD C D150 WH MB GM	1%
911401542351	DN591B LED20/TWH PSD C D150 WH WB GC	1%
911401542551	DN591B LED20/TWH PSD C D150 WH WB GM	1%
911401567271	DN588B LED6/940 PSD C D100 WH CAU	-
911401567471	DN589B LED10/940 PSD C D150 WH CAU	-
911401567671	DN590B LED15/940 PSD C D150 WH CAU	-

