



# 1F Industrial – Heavy duty

## 1F Specification Industrial

The 1F Specification Industrial is a heavy duty industrial fluorescent luminaire providing 10% uplight and 13° crosswise sheilding.

### Benefits

- Convenient installation

### Features

- Multiple knockouts
- Reflectors provide 10% uplight
- UL listed for damp locations
- Solid tops are available (no uplight)

### Application

- Industrial
- Manufacturing

### Specifications

Fixture Size	48 in, 96 in
Lamp Envelope Code	T-12, t-8
Lamp Source Code	Fluorescent

Lamp Watts	32, 59, 75, 110
Number of Lamps	2, 3, 4, 6
Voltages	120/277/347 V

## 1F Specification Industrial

### Versions

