



2F Industrial - Heavy duty

2F Specification Industrial

The 2F Specification Industrial is a heavy duty industrial fluorescent luminaire providing 25% uplight with a center "V" giving 30° crosswise shielding.

Benefits

- Convenient installation

Features

- Multiple knockouts
- Reflectors provide 25% uplight
- UL listed for damp locations

Application

- Industrial
- Manufacturing

Specifications

Fixture Size	48 in, 96 in
Lamp Watts	32, 59, 75, 110

Voltages	120/277/347 V
----------	---------------

2F Specification Industrial

Versions

