



300 - performance. Pure and Simple

300 Enclosed Downlight

The 300 LINE is a series of compact, high performance cylinder luminaires in a variety of styles and mounting configurations. The enclosed downlight style uses high intensity discharge, incandescent or fluorescent lamps. Housings are diecast aluminum with architectural twin reveals located near the luminaire aperture. A choice of two (2) light control styles and three (3) mounting options are available. Luminaires are finished with a durable textured semi-gloss TGIC powderpaint in one of six (6) standard colors.

Benefits

- Lasting durability and reliability
- Simplified mounting
- Suitable for a variety of applications
- Minimized glare

Features

- Die cast aluminum construction
- Matching brackets and one-piece luminaire
- Offers a wide choice of baffles and trims
- Recessed optical system

Application

- Education
- Municipal Buildings
- Security Lighting
- Office
- Parking Garages
- Hospitality

300 Enclosed Downlight

Versions

