



300 – performance. Pure and Simple

300 Forward Throw

The 300 LINE is a series of compact, high performance cylinder luminaires in a variety of styles and mounting configurations. The forward throw units are suitable for direct rainfall and are rain-tight, dust-tight and corrosion resistant. Housings are diecast aluminum with architectural twin reveals located near the luminaire aperture. A choice of two (2) models, two (2) light control styles and three (3) mounting options are available. Luminaires are finished with a durable textured semi-gloss TGIC powderpaint in one of six (6) standard colors.

Benefits

- Lasting durability and reliability
- Simplified mounting
- Suitable for a variety of applications
- Minimized glare

Features

- Die cast aluminum construction
- Matching brackets and one-piece luminaire
- Offers a wide choice of baffles and trims
- Recessed optical system

Application

- Education
- Municipal Buildings
- Security Lighting
- Office
- Parking Garages
- Hospitality

300 Forward Throw

Versions

