



# 940 - adding elegance and improved visibility to the low level environment

## 940 Line Brick Light

The 940 luminaire is a compact, brick-sized unit specifically designed for masonry applications or in environments requiring a smaller scale recessed fixture. The 940 is designed to accept energy saving compact fluorescent lamps up to 13W and incandescent lamps to 60W.

### Benefits

- Protected against moisture, dust and insects
- Low-glare illumination, free from streaks or striations
- Quick installation and maintenance
- Eliminates potential for misapplication
- Provides additional design flexibility

### Features

- Sealed and gasketed
- Specular Alzak hammertone reflectors
- Firmly secured reflector and electrical assembly
- Available for installation in all types of wall construction

### Application

- Walkways

## 940 Line Brick Light

### Versions

