



Clean, elegant architectural styling

Alcyon Line Voltage

Alcyon Low and Line Voltage luminaires utilize today's reliable and economical halogen and Incandescent lamps for ambient, task, accent and wall washing applications. Available in PAR20, PAR30, PAR38 and T4 halogen sources, Alcyon delivers bright light that is easily dimmable.

Benefits

- Wireless stem w/ 360° horizontal rotation
- Lamp forward design for easy relamping
- Accepts up to two accessories

Features

- Compact line voltage track adapter
- Integral Accessory cartridge
- Available in Par20/30/38 and T4 lampings

Application

- Fashion
- Food and Large Retailers

Alcyon Line Voltage

Versions

