



BL616 - showcasing the best features of your landscape

BL616 Micro Accent

The BL616 is made with die-cast aluminum and has a fully adjustable swivel arm with vibration-proof locking teeth. Available in low voltage incandescent and LED sources.

Benefits

- Ensures long-lasting durability
- Able to direct light with ultimate precision
- Offers up to 25,000 hour life with LED
- Provides added corrosion resistance
- Quick and easy installation

Features

- Die-cast aluminum construction
- Fully-adjustable swivel arm with vibration-proof locking teeth
- Available with warm or cool LEDs
- Thermoset powdercoat finish
- Pre-wired

Application

- Landscape

BL616 Micro Accent

Versions

