



# AR - adding a touch of originality to any project

## Bracket (AR)

The AR mounting arms feature a cast-aluminum curved arm and a decorative element welded to a cast-aluminum plate. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The AR plates are mechanically fastened using stainless steel hardware to a central pole adaptor slip-fitting 9" (229 mm) over a 4" (102 mm) O.D. pole or tenon. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php" target="\\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 1.35

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (AR)

### Versions

