



# CN1 - adding a touch of originality to any project

## Bracket (CN1)

The CN1 mounting arm features two 2" by 3" (51 x 76 mm) rectangular extruded aluminum arms welded to the central pole adaptor. The mounting arm includes a cast-aluminum decorative curved section welded to the central pole adaptor and the arm. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The central pole adaptor slip-fits 12" (305 mm) into a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. ~LT~br~GT~ ~GT~ The CN1 is available with the OV option that can accommodate up to two 175W ballasts. ~LT~br~GT~ ~GT~ For pole supplied by others, we strongly recommend the OV option. ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\_en.php" target="\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 2.62

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (CN1)

### Versions

