



CNB-M – adding a touch of originality to any project

Bracket (CNB-M)

The CNB-M mounting arm features a 2" by 3" (51 by 76 mm) rectangular extruded aluminum arm welded to a cast-aluminum wall-mounted housing. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system.~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php" target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Single Configuration
- EPA of 0.38

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (CNB-M)

Versions

