



# CR – adding a touch of originality to any project

## Bracket (CR)

The CR mounting arm features a seamless 2" by 4" (51 by 102 mm) rectangular aluminum extrusion, mechanically assembled on both sides to the pole and to the luminaire adaptor. The mounting arm includes a 4" (102 mm) O.D. extruded aluminum luminaire adaptor welded to the arm for luminaire mounting. When specified with a central luminaire (configurations 3A, 4A, 4B and 5), a central pole adaptor serves to facilitate installation on site. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\\_en.php" target="\\_blank"~GT~](http://www.lumec.com/Lumec3Dv2/home/index_en.php)~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 1.11

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (CR)

### Versions

