



# CRAT - adding a touch of originality to any project

## Bracket (CRAT)

The CRAT mounting arm features a seamless 1" x 2" (25 x 51 mm) rectangular extruded aluminum tube and cast decorative scroll, welded to a cast-aluminum plate. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The CRAT plate is mechanically fastened using stainless steel hardware to a central pole adaptor slip-fitting 9" (229 mm) over a 4" (102 mm) O.D. pole or tenon. ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\_en.php" target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 1.45

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (CRAT)

### Versions

