



CRC - adding a touch of originality to any project

Bracket (CRC)

The CRC mounting arm features a 2" by 3" (51 by 76 mm) rectangular extruded aluminum arm welded to a cast-aluminum wall-mounted housing. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. extruded aluminum tube and cast decorative scroll, welded to a cast-aluminum plate. The mounting arm is equipped with a 4" round (102 mm) by 4" high (102 mm) tenon for luminaire mounting. The CRC plate is mechanically fastened using stainless steel hardware to a central pole adaptor slip-fitting 9" (229 mm) over a 4" (102 mm) O.D. pole or tenon. ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php" target="_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Available in a variety of mounting configurations
- EPA of 1.39

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (CRC)

Versions

