



CRF – adding a touch of originality to any project

Bracket (CRF)

The CRF mounting arms feature a cast-aluminum curved arm mechanically assembled to a cast-aluminum plate. The mounting arms are equipped with a 4" round (102 mm) by 4" high (102 mm) tenon for luminaire mounting. The CRF plates are mechanically fastened by stainless steel hardware to a central pole adaptor slip-fitting 9" (229 mm) over a 4" (102 mm) O.D. pole or tenon. ~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php" target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Available in a variety of mounting configurations
- EPA of 1.34

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (CRF)

Versions

