



# CRI - adding a touch of originality to any project

## Bracket (CRI)

The CRI mounting arm features one 2" by 2" (51 x 51 mm) square extruded-aluminum arm welded to the central pole adaptor and closed by a cast-aluminum cover. The mounting arm includes a 1 1/4" O.D. (32 mm) cast-aluminum decorative curved section welded to both the central pole adaptor and the arm. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The aluminum central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon.

[~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php)

target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 2.68

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (CRI)

### Versions

