



# IF - adding a touch of originality to any project

## Bracket (IF)

The IF mounting arm features a 2 3/8"-O.D. (60 mm) extruded-aluminum tube bent at a 180° angle and mechanically assembled to the pole using a cast-aluminum mounting adaptor. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. ~LT~[http://www.lumec.com/Lumec3Dv2/home/index\\_en.php](http://www.lumec.com/Lumec3Dv2/home/index_en.php)~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 1.41

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (IF)

### Versions

