



# M20H - adding a touch of originality to any project

## Bracket (M20H)

The M20H mounting arm features a 2 7/8" round (73 mm) double-bend extruded-aluminum tube, welded to a cast-aluminum clamp-on pole adaptor. Comes with a standard decorative pole cap. The mounting arm includes a flat bent aluminum decorative element mechanically secured to the arm and pole. A suspended luminaire adaptor is mechanically secured to the arm by a decorative cast-aluminum clamp and stainless steel hardware. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The mounting arm clamp is mechanically assembled on a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) pole using stainless steel hardware. The location is pre-drilled on Lumec poles. ~LT~[a href="http://www.lumec.com/Lumec3Dv3/home/index\\_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable
- Clamp-on

### Features

- Available in a variety of mounting configurations
- EPA of 1.76
- Decorative pole cap included

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (M20H)

### Versions

