



# M30 – adding a touch of originality to any project

## Bracket (M30)

The M30 mounting arm features a 2 3/8" round (60 mm), extruded-aluminum tube, welded to a cast-aluminum clamp-on pole adaptor. Comes with a standard decorative pole cap. The mounting arm includes a decorative curved 1.66" round (42 mm) extruded bent aluminum piece is mechanically secured to the pole using a clamp and welded to the luminaire adaptor. The mounting arm includes a 4" (102 mm) O.D. extruded aluminum luminaire adaptor welded to the arm for luminaire mounting. The mounting arm clamp is mechanically assembled on a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) pole using stainless steel hardware. The location is pre-drilled on Lumec poles. [http://www.lumec.com/Lumec3Dv2/home/index\\_en.php](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable
- Clamp-on

### Features

- Available in a variety of mounting configurations
- EPA of 1.56
- Decorative pole cap included

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (M30)

### Versions

