



## MT - adding a touch of originality to any project

### Bracket (MT)

The MT mounting arm features a 2 3/8" round (60 mm) extruded-aluminum arm welded to an aluminum central pole adaptor. The mounting arm includes a decorative bent extruded-aluminum tube welded to the central pole adaptor and to the luminaire adaptor. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The aluminum central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon.~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\_en.php" target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

#### Benefits

- Decorative, yet durable

#### Features

- Available in a variety of mounting configurations
- EPA of 2.20

#### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (MT)

### Versions

