



MT – adding a touch of originality to any project

Bracket (MT)

The MT mounting arm features a 2 3/8" round (60 mm) extruded-aluminum arm welded to an aluminum central pole adaptor. The mounting arm includes a decorative bent extruded-aluminum tube welded to the central pole adaptor and to the luminaire adaptor. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The aluminum central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon.~LT~[a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php"](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Available in a variety of mounting configurations
- EPA of 2.20

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (MT)

Versions

