



RSAR - superior strength

Bracket (PSA)

- Made of cast A356 aluminum, mechanically assembled to the pole.
 - Available for a 2.375"(60mm), 3"(76mm) or 4" (102mm) round pole.
 - Available with RoadStar Only.
 - Consult Factory to insure compatibility with your pole and fixture.
- [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php"](http://www.lumec.com/Lumec3Dv2/home/index_en.php)
target="_blank"~GT~LT~b~GT~Lumec3D: Online 3D
Configurator~LT~/b~GT~LT~/a~GT~

Benefits

- Ensures lasting durability

Features

- Cast aluminum construction
- Fits round poles of various sizes
- Available with RoadStar luminaires

Application

- Road and Street