



# RLAR - superior strength

## Bracket (RLAR)

• Made of cast A356 aluminum, mechanically assembled to the pole. • Available for a 4" (102mm) to 4.9" (124mm) or 5" (127mm) to 6" (152mm) round or 4" (102mm) minimum square pole. • Available with Helios, RoadView, RX series, MiniView, RoadFocus and StreetView. • Consult Factory to insure compatibility with your pole and fixture. ~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\_en.php" target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~b~GT~LT~a~GT~

### Benefits

- Ensures lasting durability

### Features

- Cast aluminum construction
- Fits round and square poles of various sizes
- Available with Helios, RoadView, RX Series, and StreetView luminaires

### Application

- Road and Street