



Precision and Performance

Calculite LED 4" Adjustable Accent

Calculite LED 4" Adjustable Accent Finishing Reflector design augments the precision of the optical design to produce a unique accent luminaire. Finishing Reflector provides discrete, low luminance appearance while allowing maximum lighting efficacy.

Benefits

- Five reflector finishes with three flange options available
- Telescoping mounting bars come pre-installed with residential and commercial frames
- Four beam spread options offering field replaceable lighting customization

Features

- Die-cast aluminum ring provides 366° horizontal rotation and locks with finger tab (no tools required)
- The Light Engine assembly keeps the source of brightness at a 50° cutoff when the fixture is at nadir
- Adjustments are set while the Light Engine is powered, reducing the time required to aim the fixture by up to 50% compared to conventional designs
- Developed with Precision Optics, that maintain proper alignment between the light source and reflector throughout the range of adjustment providing maximum light output and glare control

Application

- Residential
- Office
- Banks
- Hospitality
- Airports
- Fashion

Calculite LED 4" Adjustable Accent

Versions

