



# Experience the change, see the difference

## Calculite LED 6" cylinder gen 3

Calculite 6" Cylinder Gen3 features industry leading visual comfort and excellent uniform illumination over time.

### Benefits

- 3 different cylinder and reflector options to satisfy a variety of applications
- Maximize visual appeal by three beam spreads options to give the right distribution and light output
- Ultimate user comfort by providing 50 degree physical and 45 degree reflected cutoff, creating less brightness
- Uniform light and color consistency at an SDCM of 2
- Smooth, sleek, and new smaller overall design

### Features

- L90 (90% lumen maintenance) up to 60,000 hrs. and efficacies as high as 115 lm/W
- 3 cylinder options: Surface, Wall, and Pendant
- 3 reflector options: Downlight, Wall Wash, and Double Wall Wash
- Narrow, Medium, Wide beam options in all lumen packages
- Dimming options: Standard dimming to 1% for 0-10V, ELV

### Application


- Residential
- Office
- Banks
- Hospitality
- Airports
- Fashion

## Calculite LED 6" cylinder gen 3

### Versions



### Accessories



Ordercode SWZDT

