



Calculite Tunable White solutions allow the freedom to create different ambiances in a variety of applications.

Calculite LED tunable white gen 3

Lightolier tunable white lighting solutions provide more than illumination. Through a combination of light quality, color, and intensity they help create environments that can be tailored to occupants' needs and preferences. .

Benefits

- Personal Control: Get more flexibility and easily change LED intensities and correlated color temperature (CCT) from warm white (2700K) to cool white (6500K).
- Scene Set: Use factory installed presets to a combination of predetermined presets instantly to set the scene for room ambiance that supports a task or spontaneous activity
- Dynamics: Automatically adjust color temperature and brightness depending on time of day or task

Features

- Easy specification: use the same Calculite frame and reflector with the tunable white light engine
- Available in 4", 6", 7", round & square apertures
- CCT color tunability: 2700K to 6500K

Calculite LED tunable white gen 3

Application

- Residential
- Office
- Banks
- Hospitality
- Airports
- Fashion

Versions

