



# ClassicStyle - modern functionality in a timeless design

## ClassicStyle Post Top LED (VLR)

Now you can enjoy high-performing, energy-saving LED technology without worrying about the harsh glare or pixelization that can occur with LED luminaires. With the full, comfortable glow of new Lumec ClassicStyle Luminaires with ClearGuide Technology, you can breathe new life into nighttime city spaces, strengthen a community bond, and enhance a sense of security throughout the night. This state-of-the-art, outdoor urban post top luminaire use a revolutionary, unique, vertically-oriented light engine that creates transparency during the day while at night, the center comes to life with full illumination, and free from the glare typically found in standard LED technologies. ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\_en.php" target="\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Enhanced visual comfort
- Creates a cohesive aesthetic throughout your space
- Ensures lasting durability and reliability
- Protected against moisture, dust and insects
- Increased connectivity possibilities

### Features

- Utilizes Philips ClearGuide technology
- Provides a family of luminaires
- Acrylic or Polycarbonate globe
- IP66 rated
- 5-pin and 7-pin NEMA receptacles available

## ClassicStyle Post Top LED (VLR)

### Application

- Road and Street
- Bridges, Monuments, Facades

### Versions

