



Aesthetically pleasing

Coffaire Fluorescent HP

Coffaire HP (High Performance): Our new high-performance Coffaire HP luminaire features a high 95% reflectance white powder painted body, our new Transoptix lens and a 95% reflectance MIRO aluminum reflector. Achieving efficiencies 20% greater than comparable luminaires currently available in the market.

Benefits

- Can be continuous row mounted

Features

- Perforated mesh lamp basket with unique TransOptix lens
- Same fixture fits both G and T ceiling types
- Only 5 deep
- Suitable for damp locations

Application

- Office
- Hospitality
- Education

Versions

