



# CRG Cleanroom - Superior and practical

## CRG Series Recessed Cleanroom

The CRG Containment Series is designed to meet the criteria for critical environments in recessed grid applications.

### Benefits

- Designed to meet the criteria for critical environments

### Features

- Suitable for wet locations
- Suitable for Class 100, 1,000 , 10,000, 100,000 environments
- Captive stainless steel Phillips flat head fasteners are standard

### Application

- Laboratories
- Manufacturing
- Pharmaceuticals
- Medical

## CRG Series Recessed Cleanroom

### Versions

