



CUL16 - offering a distinctive appearance to any outdoor landscape

CUL16 Copper Accent

Hadco's CUL family of path lights are low voltage landscape luminaires offering a distinctive appearance to any outdoor application. The fixtures are hand crafted with a spun solid copper roof with copper stem. Optics includes a reflective white powdercoat on underside of roof with frosted tempered glass lens. Also available with a Philips MR16 LED lamp.

Benefits

- Natural aging color
- Able to direct light with ultimate precision
- Offers 25,000 hour life with LED
- Easy hookup to the low voltage supply cable
- Holds lamps securely in place

Features

- Machined solid copper housing
- Fully-adjustable natural brass swivel arm and fastener
- Available with 5.5W MR16 LED lamp
- Pre-wired
- S7 mounting stake included
- Stainless steel retention clip affixed to socket

Application

- Landscape

CUL16 Copper Accent

Versions

