



# Emergency Ballast

## DEB Low Profile Emergency Ballast

The Chloride DEB Low profile Series fluorescent emergency ballast are designed to be field installed into a wide range of fluorescent luminaires. When AC power fails these units work in conjunction with the AC ballast to convert the fixture into an emergency lighting fixture. DEB Series fluorescent ballast switches to emergency mode, keeping one or two lamps illuminated for a minimum of 90 minutes. These emergency ballast are compatible with electronic, standard, energy saving and dimming ballast.

### Benefits

- Carries the load of the luminaire until the generator comes online

### Features

- Suitable for indoor and damp locations when installed inside of fixtures rated for wet locations
- Dual input voltage 12/277

### Application

- Exit and Emergency

### Versions

