



# Emergency Ballast

## DEB-8W Emergency Ballast

The DEB CFL emergency ballasts are used in the event of a power loss, the ballast immediately carries the load of the light, until the generator comes online. They light the specified number of lamps to approximately half brightness to assist in egress from the building. The model are used in compact fluorescent luminaires.

### Benefits

- Carries the load of the luminaire until the generator comes online

### Features

- Dual voltage--12/277VAC, 6 Hz
- High temperature nickel-cadmium batteries
- 22-gauge steel cases

### Application

- Exit and Emergency

### Versions

