



# Designer Floodlight - combining impressive floodlighting performance and control

## Designer Floodlight DF12

The DF12 designer floodlight from Gardco provides remarkable floodlighting performance and control from a soft, handsome architectural form. This comparatively compact unit utilizes metal halide and high pressure sodium lamps up to 750W which, in combination with the 5 precision optical systems, creates opportunities for illumination levels and wide luminaire spacings which had not been previously achievable. A sophisticated high performance luminaire doesn't have to look utilitarian. The graceful styling and elimination of decorative elements assures that the designer floodlight will blend effortlessly with landscapes and architecture. Whether ground mounted, wall mounted or pole mounted, the timeless form of the DF12 will be appropriate at the site for years to come.

### Benefits

- Protected against moisture, dust, pollutants and insects
- Suitable for a variety of applications
- Optimal lighting and glare control
- Ensures durable and reliable performance
- Seamlessly blends into its surroundings

### Features

- Thoroughly sealed and gasketed
- Offers a variety of precision optical systems
- Die cast aluminum construction
- Small profile

## Designer Floodlight DF12

### Application

- Arena and Sports
- Bridges, Monuments, Facades
- Security Lighting
- Sign Lighting
- Walkways

