



Designer Floodlight - combining impressive floodlighting performance and control

Designer Floodlight DF7

The first measure of a superior flood is lighting performance.. controlled, uniform and efficient distributions that offer clean, unstriated light, wide fixture spacings and elimination of glare at normal viewing angles. Gardco's four interchangeable, precision optical systems set new standards for each of these important criteria. The severity of the elements, in addition to maintenance equipment, sprinklers and vandals, make the low-level environment a harsh one. The Gardco floodlight is a formidable opponent, with die cast housing construction, rugged mounting knuckle and tamper-resistant fasteners, all protected by a textured polyester powdercoat finish, silicone seals and moisture-proof gaskets. Above all, the DF7 is versatile. Choice of lamps up to 250W metal halide, four optical systems and numerous mounting options provide a lighting fixture which effortlessly accommodates the multitude of floodlighting challenges.

Benefits

- Protected against moisture, dust, pollutants and insects
- Suitable for a variety of applications
- Optimal lighting and glare control
- Ensures durable and reliable performance
- Seamlessly blends into its surroundings

Designer Floodlight DF7

Features

- Thoroughly sealed and gasketed
- Offers a variety of precision optical systems
- Die cast aluminum construction
- Small profile

Application

- Arena and Sports
- Bridges, Monuments, Facades
- Security Lighting
- Sign Lighting
- Walkways

Versions

