



# FlexScape – Your ultimate landscape lighting chameleon

## FlexScape LED accent line voltage landscape luminaire (B9)

With the unique convenience of field adjustable beam patterns and lumen outputs, Hadco FlexScape LED line-voltage inground and accent landscape luminaires deliver powerful luminaire performance in a small form factor that integrates seamlessly throughout your commercial landscape projects. The LED Accent version brings landscape lighting to the next level. Designed for optimal LED performance, it provides the lighting professional with countless line-voltage options.

### Benefits

- Multi-tasking accent and inground line-voltage luminaires pack a powerful punch in a compact form factor
- Discretely tucked into the surrounding landscape to ensure that the focus remains on your design intent
- Easily adapt the lighting to seasonal, special event and needs-based changes with the field adjustable beam patterns and lumen outputs

### Features

- Lumen output ranging from approximately 1000 to 3,500 lumens
- Five field adjustable lumen outputs
- Narrow, medium and wide flood beam patterns, interchangeable via snap-on lenses
- Wired for standard 0-10V dimming
- IP66 rated luminaire

## FlexScape LED accent line voltage landscape luminaire (B9)

### Application

- Bridges, Monuments, Facades
- Sign Lighting
- Landscape
- Bridges, Monuments, Facades
- Sign Lighting
- Landscape

### Versions

