



GP Flood – versatility with scale

GP Flood Series – GP4

The GP4 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP4 Flood series is available with ED28 lamps for pulse start metal halide and ED18 lamps for high pressure sodium up to 400 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The GP4 is also available in 55W and 85W very-long life induction sources for 100,000 hours.

Benefits

- Suitable for a variety of applications
- Ensures cool operation
- Durable and reliable construction
- Quick and easy maintenance
- Ensures lasting performance in harsh environmental conditions

Features

- Offers a variety of optical distributions
- Integral heat sink
- Die cast aluminum housing
- Hinged lens
- IP65 rating

GP Flood Series - GP4

Application

- Arena and Sports
- Bridges, Monuments, Facades
- Security Lighting
- Sign Lighting
- Walkways

