



# GUL Series - Aesthetic and efficient

## GUL Series Louvered Uplight High Bay

An aesthetically pleasing, high efficiency fluorescent high-bay that provides exceptional light distribution for general areas with a design that allows for up-light. The unique louver is shaped to conform with the arch bottom of the GUL. The clean and crisp look of the GUL coupled with the up-light component make it an ideal choice for retail applications. Applications include supermarkets, retail, lobbies and museums.

### Benefits

- Sturdy and rigid luminaire
- Good optical performance
- Provides uplight
- Fits many applications

### Features

- Heavy gauge cold rolled steel housing
- Precision aluminum reflector
- Standard 15 cell shielding louver
- Multiple mounting methods

### Application

- Manufacturing
- Industrial
- Retail

# GUL Series Louvered Uplight High Bay

## Versions

