



Gullwing LED - the grace and style of Gullwing with the efficiency and sustainability of LED

Gullwing Area Small LED GL13

Successfully merging practical engineering, sleek aesthetics and industry-leading LED performance into a luminaire of distinctive design and style, the Gullwing LED promptly set a new standard in energy-efficient area illumination. Now these identical qualities have been scaled down, creating a luminaire that is ideal for use on walkways, bicycle paths and in park settings. Developed for mounting heights of 15' to 20' and lower, the GL13 Gullwing LED effectively combines the energy-saving performance and graceful aesthetics that are essential for modern-day lower level lighting applications. Construction Rugged die cast aluminum construction, concealed hardware, comprehensive gasketing and fade and abrasion resistant finishes combine to create a luminaire of enduring quality. Performance Within this streamlined luminaire is an LED array system that delivers one of four unique distribution patterns. This system provides improved light output and a longer lifespan than traditional sources, while consuming a small fraction of the power. Maintenance Ease Toolless access for installation and service is a Gardco trademark. A quick entry door handle provides complete access to the luminaire's optical, electrical and mounting hardware systems.

Benefits

- Improved light output and lifetime over traditional sources
- Eliminates need for a support arm
- Easy installation and maintenance
- Enduring quality and reliability
- Fade and abrasion resistant

Gullwing Area Small LED GL13

Features

- One-piece die cast aluminum housing
- Mounts directly to a pole or wall
- Integral extruded aluminum thermal radiation fins
- Tool-less access to internal components
- Sleek profile and rugged construction

Application

- Parks and Plazas
- Road and Street


Accessories



Ordercode Prog MR



Ordercode Prog MR Rem



Ordercode Prog MR Optics



Ordercode SiteWise

