



# GUN Series - Aesthetic and efficient

## GUN Series Uplight High Bay

An aesthetically pleasing, high efficiency fluorescent high-bay that provides exceptional light distribution for general areas with a narrow design that allows for up-light. The clean and crisp look of the GUN coupled with the up-light component make it an ideal choice for retail applications. Other applications include warehouses, manufacturing facilities, museums, hotels and gymnasiums with the wireguard safety option.

### Benefits

- Sturdy and rigid luminaire
- Good optical performance
- Provides uplight
- Fits many applications

### Features

- Heavy gauge cold rolled steel housing
- Precision aluminum reflector
- High efficiency prismatic lens standard
- Multiple mounting methods

### Application

- Manufacturing
- Industrial
- Warehouse
- Retail

## GUN Series Uplight High Bay

### Versions

