



# HBO - Traditional and efficient

## HBO Open High Bay Aluminum Reflector

The HBO Open High Bay Luminaire features open spun aluminum reflectors for maximum efficiency in general purpose retail, educational and industrial applications.

### Benefits

- Heavy duty construction
- Cooler operation for longer life
- Field adjustable light distribution
- Provides uplight

### Features

- Two piece die cast aluminum housing
- Day-Brite "Slant 2" ballast mounting
- Heavy gauge adjustable yoke for reflector mounting
- Precision spun aluminum reflector

### Application

- Manufacturing
- Industrial
- Warehouse

## HBO Open High Bay Aluminum Reflector

### Versions

