



HighFocus – Above all, maximizing efficiencies with light

HighFocus LED high mast (HFL)

Lumec HighFocus LED high mast luminaires provide an energy saving, lowmaintenance solution that provides managers and work crews with the freedom to focus on other tasks. HighFocus LED features scalable lumen packages and offers up to 97,389 lumens.

Benefits

- Provides reliable and uniform LED illumination ranging from 400 to 1000W HID replacement
- Consistent and uniform light levels mean that anyone can confidently navigate the well-lit area with ease
- Three lumen packages available providing up to 97,389 lumens
- Long LED life means that drivers aren't frequently inconvenienced by maintenance-related lane or area closures.
- Includes <http://www.usa.lighting.philips.com/products/product-highlights/service-tag> Service Tag, Philips innovative way to provide assistance throughout the life of the product.

Features

- LED illumination ranging from 400 to 1000W HID replacement.
- Three lumen packages available providing up to 97,389 lumens
- Entire optical assembly rotatable,
- IP66 Rated light engines
- Optional 5-pin and 7-pin NEMA twist lock receptacles available

Application

- Road and Street

HighFocus LED high mast (HFL)

Versions

