



HP - High performance

HP High Performance Industrial

The HP High Performance Industrial utilizes a specialized specular reflector to provide high vertical illumination and/or concentrated task lighting.

Benefits

- Concentrates light under luminaire for high illumination levels
- Convenient installation
- Designed to withstand corrosion

Features

- Narrow light distribution
- Excellent for shelf or stack lighting in tall or narrow aisles
- Multiple knockouts
- Suitable for unit or row mounting
- UL listed for damp locations

Application

- Manufacturing
- Industrial
- Warehouse

HP High Performance Industrial

Versions

