



i25 Inground – durable and discreet illumination

i25 Inground

The revolutionary i2.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench – the i2.5 reinforces HADCO's position as the leader in landscape lighting. Now available with LED

Benefits

- Ensures long-lasting durability
- Creates a variety of effects
- Up to 50,000 hour life with LED module
- High-impact resistance
- Dust-tight, dual-rated, sealed against direct jets of water and continuous immersion

Features

- Single-piece composite housing includes separate sealed compartments
- Available with a variety of light sources, including LED lamps and modules
- Tempered borosilicate lens
- IP66/68 rated

Application

- Landscape

i25 Inground

Versions



Accessories



Ordercode CPS25



Ordercode I25CRGN



Ordercode I25CRGSS



Ordercode I25FRL



Ordercode I25HDN



Ordercode I25HDSS



Ordercode I25SRL

